



ADVANCING SURGICAL **POSSIBILITIES**

Spine Solutions

Midas Rex™ **MR8™**
High-Speed Drill System

Medtronic
Further. Together

The Midas Rex™ MR8™ high-speed drill system is engineered and ergonomically crafted to deliver **smooth, precise bone cutting performance**, and seamlessly integrates navigated drilling with StealthStation™ S8. And with our comprehensive support, education, training, and in-field service, you have a partner that's there for you from start to finish.

Midas Rex™ MR8™. It's not just a drill. It's advancing surgical possibilities.

CONTROLLED PRECISION

So you can be confident during your procedures.

- Attachment technology engineered to deliver smooth, precise bone cutting
- Ergonomically crafted to perfectly balance in hand, it's lighter than previous models to minimize hand fatigue
- Efficient electric motor technology designed for lengthy drill times
- Power and performance tailored to efficiently shave through bone and biomaterials



MORE APPLICATIONS MORE OPTIONS

The MR8™ platform delivers more procedural flexibility than ever for spine applications.

- Designed for use during lumbar spine approaches including:
 - Microdiscectomy
 - Decompression
 - Posterior Lumbar Interbody Fusion
 - Transforaminal Lumbar Interbody Fusion
 - Anterior Lumbar Interbody Fusion
 - Direct Lumbar Interbody Fusion
- Now featuring 18 cm small bore attachments in straight, angled, and double-lock configurations
- Expanded metal-cutting options – longer 14 cm attachment and 3.2 mm cutter



VERSATILE ACCESS

Our wide range of attachments have been designed to provide a more streamlined profile with flexible options you can tailor for that unique situation. So you have improved visualization and increased accessibility of the surgical site.

Streamlined Attachment Profiles

Improved line-of-sight and reach into tighter spaces

Telescoping Tools & Attachments

All telescoping tubes feature tapered MIS tips for improved site visibility


Midas Rex™ MR8™ ClearView™ Spine

- Shorter attachment hub for improved access
- Integrated irrigation delivery sleeve extended closer to cutting tip
- Better surgical visibility and access for minimally invasive surgeries



Stealth-Midas™ MR8™

- Drill with real-time visual feedback
- Expanded range of navigable tools from 9 to 22
- Improved ergonomics with tracker orientation on top for angled attachments
- Quarter-turn secondary locking mechanism
- Compatible with StealthStation™ S8 with improved ease of use and tool management



ORDERING INFORMATION

MEDTRONIC CODE	DESCRIPTION
EK800	KIT MIDAS REX™ MR8™ ELECTRIC MOTOR
EK810	KIT MIDAS REX™ MR8™ ELECTRIC TOUCH MOTOR
EK850	KIT MIDAS REX™ MR8™ ELECTRIC PLUS MOTOR
EK800N	KIT MIDAS MR8™ ELECTRIC MOTOR STEALTH-MIDAS™
EK001	KIT INTEGRATED POWER CONSOLE
PK800	KIT MIDAS REX™ MR8™ PNEUMATIC MOTOR
PK810	KIT MIDAS REX™ MR8™ PNEUMATIC TOUCH MOTOR
PK800N	KIT MIDAS MR8™ PNEUM MOTOR STEALTH-MIDAS™
PC700	ACCY PC700 MR7/MR8™ FOOT CRTL PNEUMATIC
MR8-AS10	ATT MR8™ 10 CM STRAIGHT 2.4 MM
MR8-AA10	ATT MR8™ 10 CM ANGLED 2.4 MM
MR8-AA10DK	ATT MR8™ 10 CM ANGLED DK 2.4 MM
MR8-AVS10	ATT MR8™ 10 CM VARIABLE STRAIGHT 2.4 MM
MR8-AVA10	ATT MR8™ 10 CM VARIABLE ANGLE 2.4 MM
MR8-AVA10DK	ATT MR8™ 10 CM VARIABLE ANG DK
MR8-AS12	ATT MR8™ 12 CM STRAIGHT 2.4 MM
MR8-AA12	ATT MR8™ 12 CM ANGLED 2.4 MM
MR8-AA12DK	ATT MR8™ 12 CM ANGLED DK 2.4 MM
MR8-AVS12	ATT MR8™ 12 CM VARIABLE STRAIGHT 2.4 MM
MR8-AVA12	ATT MR8™ 12 CM VARIABLE ANGLE 2.4 MM
MR8-AVA12DK	ATT MR8™ 12 CM VARIABLE ANG DK
MR8-AS14	ATT MR8™ 14 CM STRAIGHT 3.2 MM
MR8-AA14	ATT MR8™ 14 CM ANGLED 3.2 MM
MR8-AA14DK	ATT MR8™ 14 CM ANGLED DK 3.2 MM
MR8-AVS14	ATT MR8™ 14 CM VARIABLE STRAIGHT 3.2 MM
MR8-AVA14	ATT MR8™ 14 CM VARIABLE ANGLE 3.2 MM
MR8-AVA14DK	ATT MR8™ 14 CM VARIABLE ANG DK

MEDTRONIC CODE	DESCRIPTION
MR8-AS15	ATT MR8™ 15 CM STRAIGHT 2.4 MM
MR8-AA15	ATT MR8™ 15 CM ANGLED 2.4 MM
MR8-AA15DK	ATT MR8™ 15 CM ANGLED DK 2.4 MM
MR8-AVS15	ATT MR8™ 15 CM VARIABLE STRAIGHT 2.4 MM
MR8-AVA15	ATT MR8™ 15 CM VARIABLE ANGLE 2.4 MM
MR8-AVA15DK	ATT MR8™ 15 CM VARIABLE ANG DK
MR8-AS18	ATT MR8™ 18 CM STRAIGHT 2.4 MM
MR8-AA18	ATT MR8™ 18 CM ANGLED 2.4 MM
MR8-AA18DK	ATT MR8™ 18 CM ANGLED DK 2.4 MM
MR8-AS21	ATT MR8™ 21 CM STRAIGHT 3.2 MM
MR8-AA21	ATT MR8™ 21 CM ANGLED 3.2 MM
MR8-AA21DK	ATT MR8™ 21 CM ANGLED DK 3.2 MM
MR8-AS26	ATT MR8™ 26 CM STRAIGHT 3.2 MM
MR8-AT10	ATT MR8™ TELESCOPING BASE
MR8-AT10DK	ATT MR8™ TELESCOPING BASE DOUBLE LOCK
MR8-AT10ADK	ATT MR8™ TELESCOPING BASE ANGLE DOUBLE LK
MR8-TT12MIS	TUBE MR8™ 12 CM TELESCOPING STRAIGHT
MR8-TT12AMIS	TUBE MR8™ 12 CM TELESCOPING ANGLE
MR8-TT12CMIS	TUBE MR8™ 12 CM TELESCOPING CURVE
MR8-TT12FMIS	TUBE MR8™ 12 CM TELESCOPING FINE
MR8-TT14MIS	TUBE MR8™ 14 CM TELESCOPING STRAIGHT
MR8-TT14AMIS	TUBE MR8™ 14 CM TELESCOPING ANGLE
MR8-TT14CMIS	TUBE MR8™ 14 CM TELESCOPING CURVED
MR8-TT15H	TUBE MR8™ 15 CM TELESCOPING HOODED
MR8-TT18MIS	TUBE MR8™ 18 CM TELESCOPING STRAIGHT
MR8-TT18H	TUBE MR8™ 18 CM TELESCOPING HOODED

Medtronic

4620 N. Beach St.
Fort Worth, TX 76137 USA
Toll free: (800) 433-7080
Fax: (800) 468-9713

medtronic.com

UC202000972aEN © 2020 Medtronic. All rights reserved. Medtronic, Medtronic logo and Further, Together are trademarks of Medtronic.

CAUTION: Federal Law (USA) restricts these devices for sale by or on the order of a physician. Refer to product instruction manual/package insert for instructions, warnings, precautions and contraindications. Healthcare professionals must review the product technical manual prior to use for detailed disclosure. For information on Indications, Safety, and Warnings, call Medtronic at (800) 328-0810. Healthcare professionals must review the product technical manual prior to use for detailed disclosure. For information on Indications, Safety, and Warnings, call Medtronic at (877) 242-9504, or visit Medtronic's website at www.medtronic.com.